

PERMA-VAULT IN-WALL SAFE

Features:

- Heavy gauge steel construction.
- No assembly required, easy installation.
- Finished with two coats of beige, oven-baked enamel.
- Uniquely designed recessed door has hidden hinge for security.
- Open door becomes a shelf for sorting or examination of contents.
- Includes one adjustable shelf.
- Available in 4" and 8" depth.



MADE IN USA

MODEL	DESCRIPTION	OUTSIDE DIMENSIONS	WEIGHT
EW-1000-4	In-Wall Safe. Equipped with Medeco high security lock	15-3/4" x 15-3/4" x 3-1/2"	18 lbs.
EW-1000-8	Standard Security lock	15-3/4" x 15-3/4" x 8"	21 lbs.
WS-100-4-M	UL approved Medeco High Security Lock	15-3/4" x 15-3/4" x 3-1/2"	18 lbs.
WS-100-8-M	UL approved Medeco High Security Lock	15-3/4" x 15-3/4" x 8"	21 lbs.
WS-200-4	Simplex Push Button Lock	15-3/4" x 15-3/4" x 3-1/2"	18 lbs.
WS-200-8	Simplex Push Button Lock	15-3/4" x 15-3/4" x 8"	21 lbs.
WS-300-4	LaGard 4700 eCam electronic lock	15-3/4" x 15-3/4" x 3-1/2"	18 lbs.
WS-300-8	LaGard 4700 eCam electronic lock	15-3/4" x 15-3/4" x 8"	21 lbs.




WS-100-4-M



**MODEL WS-300-4-ECAM SHOWN ABOVE
SIDE HINGE ONLY, NO SHELF INCLUDED**

INSTALLATION



1. Locate studs in wall. Hold PERMA-VAULT in position between the studs and scribe around the compartment with a pencil.
2. Using the pencil lines as a guide, cut out the section of wallboard and insert the In-Wall safe. Fasten safe to studs through holes in sides of the internal compartment.

3. The installed PERMA-VAULT In-Wall Safe will conceal the cutout in the wall.

The Perma-Vault In-Wall safe provides affordable security for homes, apartments, offices, hotels, motels, hospitals, nursing homes and dormitories.

PERMA-VAULT SAFE COMPANY

72 ASH CIRCLE • WARMINSTER, PA 18974

TOLL FREE- (800) 662-3360 ≈ FAX- (215) 293-9952

VISIT OUR WEBSITE: www.perma-vault.com ≈ EMAIL: sales@perma-vault.com